



# Stepper motor EMMB-ST-42-S-SS

Part number: 8156126

FESTO



## Data sheet

| Feature                                              | Value                                                                            |
|------------------------------------------------------|----------------------------------------------------------------------------------|
| Ambient temperature                                  | 0 °C...40 °C                                                                     |
| Note on ambient temperature                          | Up to 80°C with derating -2%/°C                                                  |
| Max. installation height                             | 4000 m                                                                           |
| Note on max. installation height                     | As of 1,000 m: only with derating of -1.0% per 100 m                             |
| Storage temperature                                  | -20 °C...70 °C                                                                   |
| Relative air humidity                                | 0 - 90%<br>Non-condensing                                                        |
| Conforms to standard                                 | IEC 60034                                                                        |
| Temperature class as per EN 60034-1                  | B                                                                                |
| Max. winding temperature                             | 130 °C                                                                           |
| Rating class as per EN 60034-1                       | S1                                                                               |
| Motor type to EN 60034-7                             | IM B5<br>IM V1<br>IM V3                                                          |
| Mounting position                                    | optional                                                                         |
| Degree of protection                                 | IP20                                                                             |
| Note on degree of protection                         | IP40 for motor shaft without rotary shaft seal                                   |
| Interface code, motor out                            | 42A                                                                              |
| Electrical connection 1, connection type             | Hybrid plug                                                                      |
| Electrical connection 1, connector system            | Connection pattern L5                                                            |
| Electrical connection 1, number of connections/cores | 14                                                                               |
| Note on materials                                    | RoHS-compliant                                                                   |
| Corrosion resistance class CRC                       | 0 - No corrosion stress                                                          |
| LABS (PWIS) conformity                               | VDMA24364 zone III                                                               |
| Vibration resistance                                 | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6 |
| Shock resistance                                     | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27                |
| Approval                                             | RCM trademark                                                                    |
| CE mark (see declaration of conformity)              | To EU EMC Directive<br>In accordance with EU RoHS Directive                      |
| UKCA marking (see declaration of conformity)         | To UK instructions for EMC<br>To UK RoHS instructions                            |
| Nominal operating voltage DC                         | 48 V                                                                             |

| Feature                                                     | Value                              |
|-------------------------------------------------------------|------------------------------------|
| Number of pole pairs                                        | 50                                 |
| Motor holding torque                                        | 250 Nm                             |
| Nominal torque                                              | 240 Nm                             |
| Peak torque                                                 | 250 Nm                             |
| Nominal rotary speed                                        | 600 rpm                            |
| Max. rotational speed                                       | 2700 rpm                           |
| Max. mechanical speed                                       | 9000 rpm                           |
| Stepper angle for complete step                             | 1.8 deg                            |
| Stepping angle tolerance                                    | ±5%                                |
| Nominal power rating of motor                               | 17 W                               |
| Continuous stall current                                    | 2 A                                |
| Nominal motor current                                       | 1800 A                             |
| Peak current                                                | 2 A                                |
| Motor constant                                              | 133 Nm/A                           |
| Voltage constant, phase                                     | 12100 mV/min                       |
| Phase winding resistance                                    | 2100 Ohm                           |
| Phase winding inductance                                    | 3 mH                               |
| Winding longitudinal inductivity Ld (phase)                 | 1600 mH                            |
| Winding cross inductivity Lq (phase)                        | 3 mH                               |
| Electric time constant                                      | 1400 ms                            |
| Thermal time constant                                       | 22 min                             |
| Thermal resistance                                          | 3500 K/W                           |
| Measuring flange                                            | 200 x 200 x 15 mm, steel           |
| Total mass moment of inertia of output                      | 0.035 kgcm <sup>2</sup>            |
| Product weight                                              | 300 g                              |
| Permissible axial shaft load                                | 10 N                               |
| Permissible radial shaft load                               | 28 N                               |
| Rotor position sensor                                       | Absolute single-turn encoder       |
| rotor position sensor, manufacturer designation             | Festo iC-MHM                       |
| rotor position sensor, absolute detectable revolutions      | 1                                  |
| Rotor position encoder interface                            | BiSS-C                             |
| Rotor position sensor, encoder measuring principle          | Magnetic                           |
| rotor position sensor, DC operating voltage                 | 5 V                                |
| rotor position sensor, DC operating voltage range           | 4750 V...5250 V                    |
| Rotor pos. enc., sin/cosin p/r                              | 2                                  |
| rotor position sensor, position values per revolution       | 65536                              |
| Rotor position transducer resolution                        | 16 bit                             |
| rotor position sensor, system accuracy of angle measurement | -540 arcsec...540 arcsec           |
| Mean time to failure (MTTF), subcomponent                   | 9666 years, rotor position encoder |