


Stepper motor EMMT-ST-42-S-R

Part number: 8156161

FESTO



Data sheet

Feature	Value
Ambient temperature	0 °C...40 °C
Note on ambient temperature	Up to 80°C with derating -2%/°C
Max. installation height	4000 m
Note on max. installation height	As of 1,000 m: only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90% Non-condensing
Conforms to standard	IEC 60034
Temperature class as per EN 60034-1	B
Max. winding temperature	130 °C
Rating class as per EN 60034-1	S1
Motor type to EN 60034-7	IM B5 IM V1 IM V3
Mounting position	optional
Degree of protection	IP40
Note on degree of protection	IP40 for motor shaft without rotary shaft seal IP65 for motor housing, incl. connection technology
Interface code, motor out	42A
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connector system	M17x0.75
Electrical connection 1, number of connections/cores	12
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Approval	RCM trademark c UL us - Recognized (OL)

Feature	Value
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing authority	UL E342973
Nominal operating voltage DC	48 V
Number of pole pairs	50
Motor holding torque	250 Nm
Peak torque	250 Nm
Max. rotational speed	2700 rpm
Max. mechanical speed	9000 rpm
Stepper angle for complete step	1.8 deg
Stepping angle tolerance	±5%
Continuous stall current	2 A
Nominal motor current	1800 A
Peak current	2 A
Motor constant	133 Nm/A
Voltage constant, phase	12100 mVmin
Phase winding resistance	2100 Ohm
Phase winding inductance	3 mH
Winding longitudinal inductivity Ld (phase)	1600 mH
Winding cross inductivity Lq (phase)	3 mH
Electric time constant	1400 ms
Thermal time constant	22 min
Thermal resistance	3500 K/W
Measuring flange	200 x 200 x 15 mm, steel
Total mass moment of inertia of output	0.035 kgcm ²
Product weight	370 g
Permissible axial shaft load	10 N
Permissible radial shaft load	28 N