


Stepper motor EMMT-ST-57-L-RB

Part number: 8156182

FESTO



Data sheet

Feature	Value
Ambient temperature	-15 °C...40 °C
Note on ambient temperature	Up to 80°C with derating -2%/°C
Max. installation height	4000 m
Note on max. installation height	As of 1,000 m: only with derating of -1.0% per 100 m
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 90% Non-condensing
Conforms to standard	IEC 60034
Temperature class as per EN 60034-1	B
Max. winding temperature	130 °C
Rating class as per EN 60034-1	S1
Motor type to EN 60034-7	IM B5 IM V1 IM V3
Mounting position	optional
Degree of protection	IP40
Note on degree of protection	IP40 for motor shaft without rotary shaft seal IP65 for motor housing, incl. connection technology
Interface code, motor out	57A
Electrical connection 1, connection type	Hybrid plug
Electrical connection 1, connector system	M17x0.75
Electrical connection 1, number of connections/cores	12
Note on materials	RoHS-compliant
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Approval	RCM trademark c UL us - Recognized (OL)

Feature	Value
CE mark (see declaration of conformity)	To EU EMC Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Certificate issuing authority	UL E342973
Nominal operating voltage DC	48 V
Number of pole pairs	50
Motor holding torque	1860 Nm
Peak torque	2100 Nm
Max. rotational speed	1500 rpm
Max. mechanical speed	8000 rpm
Stepper angle for complete step	1.8 deg
Stepping angle tolerance	±5%
Continuous stall current	6100 A
Nominal motor current	5200 A
Peak current	8 A
Motor constant	320 Nm/A
Voltage constant, phase	22600 mVmin
Phase winding resistance	260 Ohm
Phase winding inductance	950 mH
Winding longitudinal inductivity Ld (phase)	1750 mH
Winding cross inductivity Lq (phase)	950 mH
Electric time constant	3700 ms
Thermal time constant	30 min
Thermal resistance	1300 K/W
Measuring flange	200 x 200 x 15 mm, steel
Total mass moment of inertia of output	0.504 kgcm ²
Product weight	1660 g
Permissible axial shaft load	15 N
Permissible radial shaft load	75 N
Brake holding torque	1740 Nm
Operating voltage DC for brake	24 V
Brake current consumption	380 A
Power consumption, brake	9 W
Brake coil resistance	63800 Ohm
Brake coil inductivity	107 mH
Brake separation time	32 ms
Brake closing time	97 ms
DC brake response delay	11 ms
Max. brake no-load speed	8000 rpm
Max. friction per braking process	6000 J
Number of emergency stops per hour	1
Mass moment of inertia of brake	0.024 kgcm ²
Switching cycles holding brake	10 million idle actuations (without friction work!)