


Parallel kit
EAMM-U-145-S62-150A-288
Part number: 8157287

FESTO



Data sheet

Feature	Value
Size	145
Mounting position	optional
Gear unit ratio	1:1
Max. rotational speed	4000 rpm
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-25 °C...60 °C
Relative air humidity	0 - 95%
Degree of protection	IP40
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	2267 kgmm ²
Frictional torque independent of load	2 Nm
Transmittable torque	50 Nm
Product weight	14600 g
Interface code, actuator	S62
Interface code, motor in	140A 150A
Note on materials	RoHS-compliant