

Shock absorber retainer DADP-ES-G8-25

Part number: 8159237

FESTO



Data sheet

Feature	Value
Size	25
Mounting position	optional
Design	Stop lever
Max. impact speed	0.8 m/s
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Ambient temperature	0 °C...60 °C
Max. stop force	1100 N
Max. tightening torque	8.4 Nm
Tolerance for tightening torque	± 20 %
Product weight	503 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS-compliant
Material lever	Wrought aluminium alloy
Material screws	Galvanised steel