


Limit switch box

SRBK-CA4-YR90-R-2A-1W-C2

Part number: 8182180

FESTO



Data sheet

Feature	Value
CE mark (see declaration of conformity)	To EU EMC Directive To EU Low Voltage Directive In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions To UK regulations for electrical equipment
Note on materials	RoHS-compliant
Measured variable	Position
Measuring principle	Magnetic reed
Sensing range	0 deg...90 deg
Ambient temperature	-20 °C...70 °C
Switching output	Contacting
Switching element function	Toggle switch, single-pole
Max. output current AC	180 mA
Max. output current DC	250 mA
Max. switching capacity AC	5 W
Max. switching capacity DC	5 W
Operational voltage range AC	0 V...120 V
Operational voltage range DC	0 V...175 V
Microswitch type	Hamlin 59140-030
Electrical connection	Screw terminal
Electrical connection 1, connection type	Terminal strip
Electrical connection 1, cable outlet	Straight
Electrical connection 1, design	Angular
Electrical connection 1, connector system	Screw terminal
Electrical connection 1, number of connections/cores	10
Connectable nominal cross section conductor	0.25 mm ² ...2.5 mm ²
Cable fitting	M20x1.5
Dimensions (W x L x H)	130 mm x 85 mm x 128 mm 130 mm x 85 mm x 138 mm 130 mm x 85 mm x 158 mm 147 mm x 85 mm x 128 mm 147 mm x 85 mm x 138 mm

Feature	Value
Connection point for positioner and position sensor conforms to standard	VDI/VDE 3845 size AA 1 VDI/VDE 3845 size AA 2 VDI/VDE 3845 size AA 3
Mounting position	optional
Product weight	460 g
Housing colour	Black
Material housing	PA
Material seals	NBR
Material shaft	PA
Material screws	Stainless steel
Material mounting bracket	PA
Material snap ring	High-alloy stainless steel
Protective cap material	PC
Switching status indication	Optical
Position indicator	Yellow/red
Setting range of angular detection	0 deg...90 deg
Storage temperature	-20 °C...50 °C
Degree of protection	IP66 IP67
Protection class	II
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6
Corrosion resistance class CRC	3 - high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Pollution degree	3