



# Pressure regulator MS4-LR-1/4-D6-RG-WR

Part number: 8190240

FESTO



## Data sheet

| Feature                                               | Value                                                                                      |
|-------------------------------------------------------|--------------------------------------------------------------------------------------------|
| Size                                                  | 4                                                                                          |
| Series                                                | MS                                                                                         |
| Actuator lock                                         | Rotary knob with detent                                                                    |
| Mounting position                                     | optional                                                                                   |
| Design                                                | Directly actuated diaphragm regulator                                                      |
| Controller function                                   | Output pressure constant<br>With secondary venting<br>With return flow function            |
| Pressure gauge (ANALOG) or Pressure display (DIGITAL) | Red/green scale                                                                            |
| Operating pressure                                    | 0.08 MPa...1.4 MPa<br>0.8 bar...14 bar                                                     |
| Pressure regulation range                             | 0.3 bar...7 bar                                                                            |
| Max. pressure hysteresis                              | 0.025 MPa<br>0.25 bar<br>3.625 psi                                                         |
| Standard nominal flow rate (standardised to DIN 1343) | 1800 l/min                                                                                 |
| Operating medium                                      | Compressed air to ISO 8573-1:2010 [7:4:4]<br>Inert gases                                   |
| Note on operating and pilot medium                    | Lubricated operation possible (in which case lubricated operation will always be required) |
| Corrosion resistance class CRC                        | 2 - Moderate corrosion stress                                                              |
| LABS (PWIS) conformity                                | VDMA24364-B1/B2-L                                                                          |
| Storage temperature                                   | -10 °C...60 °C                                                                             |
| Suitable for use with food                            | See supplementary material information                                                     |
| Media temperature                                     | -10 °C...60 °C                                                                             |
| Ambient temperature                                   | -10 °C...60 °C                                                                             |
| Product weight                                        | 225 g                                                                                      |
| Type of mounting                                      | Front panel mounting<br>In-line installation<br>With accessories<br>Either:                |
| Pneumatic connection, port 1                          | G1/4                                                                                       |
| Pneumatic connection, port 2                          | G1/4                                                                                       |
| Note on materials                                     | RoHS-compliant                                                                             |

| Feature                | Value              |
|------------------------|--------------------|
| Material sub-base      | Die-cast aluminium |
| Material control panel | PA<br>POM          |
| Material seals         | NBR                |
| Material housing       | Die-cast aluminium |
| Material membrane      | NBR                |