

Toothed belt axis ELGD-TB-KF-120-300-0H-PU2

Part number: 8192365

FESTO



Data sheet

Feature	Value
Effective diameter of drive pinion	55.7 mm
Working stroke	300 mm
Size	120
Stroke reserve	0 mm
Toothed-belt pitch	5 mm
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Electromechanical linear axis With toothed belt
Type of motor	Stepper motor Servo motor
Functional principle of measuring system	Incremental
Position detection	Via inductive sensors
Max. acceleration	50 m/s ²
Max. speed	3 m/s
Repetition accuracy	±0.04 mm
Duty cycle	100%
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Storage temperature	-20 °C...60 °C
Degree of protection	IP40
Ambient temperature	0 °C...60 °C
Impact energy in end positions	1 mJ
Note on the impact energy in the end positions	At maximum homing speed of 0.01 m/s
2nd moment of area Iy	3550000 mm ⁴
2nd moment of area Iz	8985000 mm ⁴
Max. drive torque	36.2 Nm
Max. force Fy	4300 N
Max. force Fz	4300 N
Max. force Fy total axis	2957 N
Max. force Fz total axis	6500 N
Fy at theoretical life value of 100 km (only guide consideration)	17576 N

Feature	Value
Fz at theoretical life value of 100 km (only guide consideration)	17576 N
Max. idle running transfer resistance	71.8 N
Max. moment Mx	170 Nm
Max. moment My	50 Nm
Max. moment Mz	60 Nm
Max. moment Mx total axis	251 Nm
Max. moment My total axis	80 Nm
Max. moment Mz total axis	105 Nm
Mx at theoretical life value of 100 km (only guide consideration)	730 Nm
My at theoretical life value of 100 km (only guide consideration)	162 Nm
Mz at theoretical life value of 100 km (only guide consideration)	162 Nm
Distance between slide surface and guide centre	80 mm
Max. feed force Fx	1300 N
Frictional torque independent of load	2 Nm
Torsional mass moment of inertia It	1433600 mm ⁴
Mass moment of inertia JH per metre of stroke	2.792 kgcm ²
Mass moment of inertia JL per kg of working load	7.7562 kgcm ²
Mass moment of inertia JO	30.2136 kgcm ²
Feed constant	175 mm/U
Reference service life	5000 km
Maintenance interval	Life-time lubrication
Moving mass	1733 g
Product weight	13905 g
Basic weight for 0 mm stroke	10425 g
Additional weight per 10 mm stroke	116 g
Dynamic deflection (moving load)	0.05% of the axis length, max. 0.5 mm
Static deflection (load in standstill)	0.1% of the axis length
Interface code, actuator	N80
Material end cap	Aluminium gravity die-cast, painted
Material profile	Anodised wrought aluminium alloy
Note on materials	RoHS-compliant
Material cover tape	High-alloy stainless steel
Material drive cover	Aluminium gravity die-cast, painted
Material guide slide	Steel
Material guide rail	Steel
Material pulleys	High-alloy stainless steel
Material slide	Wrought aluminium alloy
Material toothed belt	Polyurethane with steel cord