


# Toothed belt axis ELGD-TB-KF-120-1000-0H-PU2

Part number: 8192369

FESTO



## Data sheet

| Feature                                                           | Value                                                              |
|-------------------------------------------------------------------|--------------------------------------------------------------------|
| Effective diameter of drive pinion                                | 55.7 mm                                                            |
| Working stroke                                                    | 1000 mm                                                            |
| Size                                                              | 120                                                                |
| Stroke reserve                                                    | 0 mm                                                               |
| Toothed-belt pitch                                                | 5 mm                                                               |
| Mounting position                                                 | optional                                                           |
| Guide                                                             | Recirculating ball bearing guide                                   |
| Design                                                            | Electromechanical linear axis<br>With toothed belt                 |
| Type of motor                                                     | Stepper motor<br>Servo motor                                       |
| Functional principle of measuring system                          | Incremental                                                        |
| Position detection                                                | Via inductive sensors                                              |
| Max. acceleration                                                 | 50 m/s <sup>2</sup>                                                |
| Max. speed                                                        | 3 m/s                                                              |
| Repetition accuracy                                               | ±0.04 mm                                                           |
| Duty cycle                                                        | 100%                                                               |
| LABS (PWIS) conformity                                            | VDMA24364-C1-L                                                     |
| Suitability for the production of Li-ion batteries                | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |
| Storage temperature                                               | -20 °C...60 °C                                                     |
| Degree of protection                                              | IP40                                                               |
| Ambient temperature                                               | 0 °C...60 °C                                                       |
| Impact energy in end positions                                    | 1 mJ                                                               |
| Note on the impact energy in the end positions                    | At maximum homing speed of 0.01 m/s                                |
| 2nd moment of area Iy                                             | 3550000 mm <sup>4</sup>                                            |
| 2nd moment of area Iz                                             | 8985000 mm <sup>4</sup>                                            |
| Max. drive torque                                                 | 36.2 Nm                                                            |
| Max. force Fy                                                     | 4300 N                                                             |
| Max. force Fz                                                     | 4300 N                                                             |
| Max. force Fy total axis                                          | 2957 N                                                             |
| Max. force Fz total axis                                          | 6500 N                                                             |
| Fy at theoretical life value of 100 km (only guide consideration) | 17576 N                                                            |

| Feature                                                           | Value                                 |
|-------------------------------------------------------------------|---------------------------------------|
| Fz at theoretical life value of 100 km (only guide consideration) | 17576 N                               |
| Max. idle running transfer resistance                             | 71.8 N                                |
| Max. moment Mx                                                    | 170 Nm                                |
| Max. moment My                                                    | 50 Nm                                 |
| Max. moment Mz                                                    | 60 Nm                                 |
| Max. moment Mx total axis                                         | 251 Nm                                |
| Max. moment My total axis                                         | 80 Nm                                 |
| Max. moment Mz total axis                                         | 105 Nm                                |
| Mx at theoretical life value of 100 km (only guide consideration) | 730 Nm                                |
| My at theoretical life value of 100 km (only guide consideration) | 162 Nm                                |
| Mz at theoretical life value of 100 km (only guide consideration) | 162 Nm                                |
| Distance between slide surface and guide centre                   | 80 mm                                 |
| Max. feed force Fx                                                | 1300 N                                |
| Frictional torque independent of load                             | 2 Nm                                  |
| Torsional mass moment of inertia It                               | 1433600 mm <sup>4</sup>               |
| Mass moment of inertia JH per metre of stroke                     | 2.792 kgcm <sup>2</sup>               |
| Mass moment of inertia JL per kg of working load                  | 7.7562 kgcm <sup>2</sup>              |
| Mass moment of inertia JO                                         | 30.2136 kgcm <sup>2</sup>             |
| Feed constant                                                     | 175 mm/U                              |
| Reference service life                                            | 5000 km                               |
| Maintenance interval                                              | Life-time lubrication                 |
| Moving mass                                                       | 1733 g                                |
| Product weight                                                    | 22025 g                               |
| Basic weight for 0 mm stroke                                      | 10425 g                               |
| Additional weight per 10 mm stroke                                | 116 g                                 |
| Dynamic deflection (moving load)                                  | 0.05% of the axis length, max. 0.5 mm |
| Static deflection (load in standstill)                            | 0.1% of the axis length               |
| Interface code, actuator                                          | N80                                   |
| Material end cap                                                  | Aluminium gravity die-cast, painted   |
| Material profile                                                  | Anodised wrought aluminium alloy      |
| Note on materials                                                 | RoHS-compliant                        |
| Material cover tape                                               | High-alloy stainless steel            |
| Material drive cover                                              | Aluminium gravity die-cast, painted   |
| Material guide slide                                              | Steel                                 |
| Material guide rail                                               | Steel                                 |
| Material pulleys                                                  | High-alloy stainless steel            |
| Material slide                                                    | Wrought aluminium alloy               |
| Material toothed belt                                             | Polyurethane with steel cord          |