


Drive shaft adapter DARF-Q13-16

Part number: 8200998

FESTO



Data sheet

Feature	Value
Size	16
Mounting position	optional
For piston diameter	Ø16
Design	Drive shaft
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-C1-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom class	Class 9 according to ISO 14644-1
Storage temperature	-20 °C...60 °C
Ambient temperature	0 °C...60 °C
Max. bending moment	4 Nm
Max. axial load static	140 N
Product weight	75 g
Type of mounting	Via through-hole and centring sleeve
Note on materials	RoHS-compliant
Drive shaft adapter material	Quenched and tempered steel