



Adaptive shape gripper kit for robots DHEF-20-A-RA50

Part number: 8210811

FESTO



Data sheet

Feature	Value
Size	20
Inverting cap version	Standard
Stroke	66 mm
Min. ø to be gripped	12 mm
Max. ø to be gripped	38 mm
Mounting position	optional
Mode of operation	Double-acting
Gripper function	Adaptive
Design	Inverting cap Force pilot operated motion sequence
Guide	Basic guide
Position detection	Via proximity switch
Pick-up tolerance	±4 mm
Placement tolerance	±2 mm
Operating pressure of ball valve drive unit	0.1 MPa...0.8 MPa 1 bar...8 bar 14.5 psi...116 psi
Operating pressure of cap	0.007 MPa...0.01 MPa 0.07 bar...0.1 bar 1.015 psi...1.45 psi
Burst pressure of cap	0.03 MPa 0.3 bar 4.35 psi
Recommended flow rate for pressure regulator	10 l/min
Max. operating frequency of gripper	1 Hz
Return-stroke time	290 ms
Advance time	270 ms
Max. speed without gripped object	290 mm/s
Max. speed during gripping	120 mm/s
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	158 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	189 N
Dynamic lateral force with max. projection	2.3 N
Contact force on the gripping object	20 N

Feature	Value
Static holding force parallel to the gripper axis	26 N
Static holding force perpendicular to the gripper axis	45 N
Impact energy in end positions	0.1 J
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation not possible
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	0 °C...60 °C
Mass moment of inertia	1.29 kgcm ²
Guide value for effective load	1 kg
Product weight	475 g
Moving mass	60 g
Note on the moving mass	Without inverting cap
Type of mounting	To ISO 9409
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cap	VMQ (silicone)
Material housing	Anodised aluminium
Locking cover material	PA
Scope of delivery	1x Velcro® roll 1x solenoid valve 1x proportional-pressure regulator 2x proximity switches 3x connecting cables
Drive system	Pneumatic