


# Guided drive DGRC-GF-16-30-PA

Part number: 8218193

**FESTO**



## Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	30 mm
Piston diameter	16 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	optional
Guide	Plain-bearing guide
Design	Guidance
Position detection	Via proximity switch
Protection against torque/guide	Guide rod with yoke
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-10 °C...60 °C
Impact energy in end positions	0.15 Nm
Max. force Fy	350.7 N
Max. force Fy static	350.7 N
Max. force Fz	350.7 N
Max. force Fz static	350.7 N
Max. moment Mx	7.54 Nm
Max. torque Mx static	7.54 Nm
Max. moment My	4.12 Nm
Max. torque My static	4.12 Nm
Max. moment Mz	4.12 Nm
Max. torque Mz static	4.12 Nm

Feature	Value
Max. permissible torque load Mx as a function of stroke	1.34 Nm
Max. effective load dependent upon stroke at defined distance xs	35.3 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	90 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	121 N
Torsional backlash	0.065 deg
Moving mass	127.6 g
Product weight	279.5 g
Basic weight for 0 mm stroke	151.9 g
Centre of gravity of moving mass as a function of stroke	27.2 mm
Pneumatic connection	M5
Note on materials	RoHS-compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material dynamic seals	TPE-U(PU)
Material end plate	Anodised wrought aluminium alloy
Material guide rod	High-alloy steel
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy steel