


Angle seat valve

VZXF-L-M22C-M-B-N2-430-H3B1-50-3

Part number: 1002544

FESTO



Data sheet

| Feature | Value |
|--------------------------------|--|
| Structural design | Poppet valve with piston actuator |
| Actuation type | Pneumatic |
| Sealing principle | Soft |
| Mounting position | Any |
| Type of mounting | Line installation |
| Cable connection | Threaded sleeve 2 NPT as per ANSI/ASME B 1.20.1 |
| Nominal width | 43 mm |
| Valve function | 2/2, closed, monostable |
| Flow direction | Non-reversible Under valve seat, for gaseous and liquid media |
| Medium pressure | 0 MPa...0.3 MPa 0 bar...3 bar |
| Nominal pressure of fitting PN | 16 |
| Exhaust air function | Without flow control option |
| Reset method | Mechanical spring |
| Type of control | Externally controlled |
| Pneumatic connection | Internal thread G1/8 |
| Operating pressure | 0.6 MPa...1 MPa 6 bar...10 bar 87 psi...145 psi |
| Medium | Vapor Hydraulic fluid based on mineral oil Inert gas Mineral oil Water Filtered compressed air, 200 µm filter mesh Neutral liquids |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Max. viscosity | 600 mm ² /s |
| Temperature of medium | -10 °C...80 °C |
| Ambient temperature | -10 °C...60 °C |
| Flow rate Kv | 23 m ³ /h |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364 zone III |

| Feature | Value |
|--|--|
| Valve housing material | Red brass |
| Material number, fitting housing | CC499K |
| Spindle seal material | NBR |
| Seat seal material | PTFE |
| Product weight | 2800 g |
| CE marking (see declaration of conformity) | as per EU pressure equipment directive |
| UKCA marking (see declaration of conformity) | according to UK regulations for pressure equipment |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Drive housing material | Brass |