


Rotary/lifting module EHMB-20-200

Part number: 1107097

FESTO



Data sheet

Feature	Value
Drive pinion diameter	6 mm
Working stroke	0 mm...200 mm
Size	20
Rotation angle	Infinite
Toothed belt pitch	2 mm
Mounting position	Any
Gearbox type	Belt drive
Structural design	Electromechanical rotary lifting module with toothed belt
Gear ratio	4.5:1
Position sensing	For inductive proximity sensors
Max. output speed	300 rpm
Max. input speed	1350 rpm
Max. speed	1.5 m/s
Repetition accuracy	±0.03°
Noise level	54 dB(A)
Information on the sound pressure level	with covering: 57 [dB (A)]
LABS (PWIS) conformity	VDMA24364 zone III
Ambient temperature	-10 °C...60 °C
Mass moment of inertia	1000 kgcm²
Max. output torque	3.15 Nm
Max. driving torque	0.7 Nm
Max. feed force Fx	480 N
No-load driving torque	0.07 Nm
Guide value for payload, horizontal	3000 g
Guide value for payload, vertical	3000 g
Product weight	1851 g
Moving mass	885 g
Material of drive shaft	Steel
Note on materials	RoHS-compliant
Material of flange	Wrought aluminum alloy, anodized
Drive shaft material	High-alloy stainless steel

Feature	Value
Cover material	Wrought aluminum alloy Anodized
Housing material	Wrought aluminum alloy Anodized
Retaining material	Wrought aluminum alloy, anodized
Retaining bracket material	Wrought aluminum alloy, anodized
Toothed belt material	Polychloroprene with glass fiber