

Parallel gripper DHPS-6-A

Part number: 1254039

FESTO



Data sheet

| Feature | Value |
|--|--|
| Size | 6 |
| Stroke per gripper jaw | 2 mm |
| Max. interchangeability | 0.2 mm |
| Max. gripper jaw angular play ax, ay | 1 deg |
| Max. gripper jaw backlash Sz | 0.02 mm |
| Rotational symmetry | 0.2 mm |
| Pneumatic gripper repetition accuracy | 0.02 mm |
| Number of gripper jaws | 2 |
| Actuator system | Pneumatic |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Gripper function | Parallel |
| Gripping force backup | Without |
| Structural design | Lever Positively driven motion sequence |
| Guide | Sliding guide |
| Position sensing | For Hall sensor |
| Operating pressure | 0.2 MPa...0.8 MPa 2 bar...8 bar 29 psi...116 psi |
| Max. operating frequency of pneumatic gripper | 4 Hz |
| Min. opening time at 6 bar | 8 ms |
| Min. closing time at 6 bar | 17 ms |
| Max. mass per external gripper finger | 10 g |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Suitability for the production of Li-ion batteries | Metals with more than 5% by mass of copper are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils |
| Ambient temperature | 5 °C...60 °C |

| Feature | Value |
|--|---|
| Gripping force per gripper jaw at 6 bar, opening | 30 N 15 N |
| Gripping force per gripper jaw at 6 bar, closing | 25 N 13.5 N |
| Mass moment of inertia | 0.008 kgcm ² |
| Maximum force on gripper jaw Fz, static | 10 N |
| Maximum torque on gripper jaw, Mx static | 0.5 Nm |
| Maximum torque on gripper jaw, My static | 0.5 Nm |
| Maximum torque on gripper jaw, Mz static | 0.5 Nm |
| Relubrication interval for guidance elements | 10 MioCyc |
| Product weight | 19 g |
| Type of mounting | With internal thread and centering sleeve Via through-hole and centering sleeve Optionally: |
| Pneumatic connection | M3 |
| Note on materials | RoHS-compliant |
| Cover cap material | PA |
| Housing material | Wrought aluminum alloy, hard-anodized |
| Gripper jaw material | High-alloy stainless steel |