

# Angled gripper DHWS-25-A-NC

Part number: 1310181

FESTO



## Data sheet

Feature	Value
Size	25
Max. interchangeability	0.2 mm
Max. opening angle	40 deg
Rotational symmetry	0.2 mm
Pneumatic gripper repetition accuracy	0.04 mm
Number of gripper jaws	2
Mounting position	Any
Mode of operation	Double-acting
Gripper function	Angle
Gripping force backup	During closing
Structural design	Lever
Position sensing	For proximity sensor
Operating pressure	4 bar...8 bar
Max. operating frequency of pneumatic gripper	3 Hz
Min. opening time at 6 bar	106 ms
Min. closing time at 6 bar	59 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper are excluded from use. Exception are printed circuit boards, cables, electrical connectors and coils
Ambient temperature	5 °C...60 °C
Mass moment of inertia	0.64 kgcm <sup>2</sup>
Maximum force on gripper jaw Fz, static	90 N
Maximum torque on gripper jaw, Mx static	3.6 Nm
Maximum torque on gripper jaw, My static	3.6 Nm
Maximum torque on gripper jaw, Mz static	3.6 Nm
Product weight	265 g

Feature	Value
Type of mounting	With internal thread and centering sleeve Via through-hole and centering sleeve Optionally:
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover cap material	PA
Housing material	Wrought aluminum alloy Hard-anodized
Gripper jaw material	High-alloy steel