


Quarter turn actuator DSR-40-180-P

Part number: 13467

FESTO



Data sheet

Feature	Value
Size	40
Cushioning angle	0.9 deg
Adjustment range of swivel angle	0 deg...180 deg
Swivel angle	0 deg...180 deg
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	None
Operating pressure	1.5 bar...8 bar
Max. swivel frequency at 6 bar	3 Hz
Operating medium	Compressed air as per ISO 8573-1:2010 [7:::]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-10 °C...60 °C
Theoretical torque at 6 bar	20 Nm
Product weight	2400 g
Type of mounting	With through-hole
Pneumatic connection	G1/4
Drive shaft material	Steel Nickel-plated
Seals material	NBR