


Rotary actuator DSM-16-270-P1-HD-A-B

Part number: 1369117

FESTO



Data sheet

Feature	Value
Size	16
Cushioning angle	9 deg
Adjustment range of swivel angle	0 deg...246 deg
Swivel angle	0 deg...246 deg
Cushioning	Elastic cushioning rings/pads at both ends with fixed stop
Mounting position	Any
Precision adjustment	-6 deg
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	For proximity sensor
Operating pressure	0.3 MPa...1 MPa 3 bar...10 bar
Max. swivel frequency at 6 bar	1.5 Hz
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. axial force	290 N
Max. radial force	300 N
Theoretical torque at 6 bar	2.5 Nm
Permissible mass moment of inertia	0.03 kgm ²
Product weight	700 g
Type of mounting	With internal thread
Pneumatic connection	M5
Note on materials	RoHS-compliant
Drive shaft material	Steel Nickel-plated
Seals material	TPE-U(PU)
Housing material	Wrought aluminum alloy