

Rotary actuator DSM-63-270-CC-HD-A-B

Part number: 1369127

FESTO



Data sheet

Feature	Value
Size	63
Cushioning angle	17.5 deg
Adjustment range of swivel angle	0 deg...240 deg
Swivel angle	0 deg...240 deg
Cushioning	Pneumatic shock absorber at both ends
Mounting position	Any
Precision adjustment	-3 deg
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	For proximity sensor
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar
Max. swivel frequency at 6 bar	0.5 Hz
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Max. axial force	1300 N
Max. radial force	1600 N
Theoretical torque at 6 bar	40 Nm
Permissible mass moment of inertia	0.5 kgm ²
Product weight	6660 g
Type of mounting	With internal thread
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Drive shaft material	Steel Nickel-plated
Seals material	TPE-U(PU)
Housing material	Wrought aluminum alloy