

Stepper motor EMMS-ST-87-S-S-G2

Part number: 1370482

FESTO



Data sheet

Feature	Value
Ambient temperature	-10 °C...50 °C
Storage temperature	-20 °C...70 °C
Relative air humidity	0 - 85 %
Conforms to standard	IEC 60034
Insulation protection class	B
Thermal class according to EN 60034-1	B
Rating class according to EN 60034-1	S1
Degree of protection	IP54
Electrical connection technology	Plug
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Certification	RCM compliance mark c UL us - Recognized (OL)
CE marking (see declaration of conformity)	As per EU EMC directive As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC To UK RoHS instructions
Nominal operating voltage DC	48 V
Motor holding torque	2.5 Nm
Max. rotational speed	2130 rpm
Step angle with full step	1.8 deg
Step angle tolerance	±5%
Motor nominal current	9.5 A
Voltage constant, phase	19 mVmin
Phase winding resistance	0.1 Ohm
Winding inductance phase	0.45 mH
Rotor mass moment of inertia	1 kgcm ²
Total output inertia moment	1 kgcm ²
Product weight	1950 g
Permissible axial shaft load	65 N
Permissible radial shaft load	200 N

Feature	Value
Brake holding torque	2 Nm