

ISO cylinder DSBC-80-80-PPVA-N3

Part number: 1383336

FESTO



Data sheet

Feature	Value
Stroke	80 mm
Piston diameter	80 mm
Piston rod thread	M20x1.5
Cushioning	Pneumatic cushioning, adjustable at both ends
Mounting position	Any
Conforms to standard	ISO 15552
Piston rod end	External thread
Structural design	Piston Piston rod Profile barrel
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.04 MPa...1.2 MPa 0.4 bar...12 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	1.8 J
Cushioning length	31 mm
Theoretical force at 6 bar, retracting	2721 N
Theoretical force at 6 bar, advancing	3016 N
Moving mass	1122 g
Moving mass at 0 mm stroke	810 g
Additional moving mass per 10 mm stroke	39 g
Product weight	3396 g
Basic weight with 0 mm stroke	2660 g
Additional weight per 10 mm stroke	92 g
Type of mounting	With internal thread With accessories Optionally:

Feature	Value
Pneumatic connection	G3/8
Note on materials	RoHS-compliant
Cover material	Die-cast aluminum, coated
Piston seal material	TPE-U(PU)
Material of piston	Wrought aluminum alloy
Piston rod material	High-alloy steel
Piston rod wiper material	TPE-U(PU)
Buffer seal material	TPE-U(PU)
Cushion piston material	POM
Material of cylinder barrel	Wrought aluminum alloy, smooth-anodized
Nut material	Steel, galvanized
Material of bearing	POM
Flange screws material	Steel, galvanized