


Rotary actuator DRRD-20-180-FH-PA

Part number: 1395606

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | 20 |
| Cushioning angle | 45 deg |
| Setting range of swivel angle for each end position | +10 /-100 deg |
| Swivel angle | 180 deg |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Structural design | Gear rack/pinion |
| Position sensing | For proximity sensor |
| Operating pressure | 0.3 MPa...0.8 MPa 3 bar...8 bar |
| Mode of operation | Double-acting |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Ambient temperature | -10 °C...60 °C |
| Theoretical torque at 6 bar | 2.41 Nm |
| Permissible mass moment of inertia | 0.04 kgm ² |
| Product weight | 839 g |
| Type of mounting | With through-hole With internal thread Optionally: |
| Pneumatic connection | M5 |
| Note on materials | RoHS-compliant |
| Drive shaft material | Tempered steel |
| Cover material | Wrought aluminum alloy Anodized |
| Seals material | NBR TPE-U(PU) |
| Housing material | Wrought aluminum alloy Smooth anodized |