


Air solenoid valve

VZWF-B-L-M22C-N1-275-V-1P4-6

Part number: 1492194

FESTO



Data sheet

Feature	Value
Structural design	Diaphragm valve Force pilot operated
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Magnet, upright
Type of mounting	Line installation
Fitting connection	1 NPT
Electrical connection	Form A Plug as per EN 175301-803 Rectangular design
Nominal width	27.5 mm
Valve function	2/2, closed, monostable
Manual override	None
Flow direction	Non-reversible
Medium	Compressed air as per ISO 8573-1:2010 [7:::] Inert gas Mineral oil Water Neutral liquids Other flow media on request
Nominal pressure of fitting PN	40
Pressure difference	0 MPa 0 psi
Differential pressure	0 bar
Coil characteristics	24 V DC: 11.0 W
Permissible voltage fluctuations	+/- 10 %
Medium pressure	0 MPa...0.6 MPa 0 bar...6 bar 0 psi...87 psi

Feature	Value
Max. viscosity	22 mm ² /s
Temperature of medium	-10 °C...80 °C
Ambient temperature	-10 °C...35 °C
Leak rate to EN 12266-1	A
Flow rate Kv	11 m ³ /h
Standard nominal flow rate	11750 l/min
On switching time	275 ms
Switching time off	290 ms
Note on materials	RoHS-compliant
LABS (PWIS) conformity	VDMA24364 zone III
Housing material	Cast brass
Material number of housing	CW617N
Seals material	FPM
Material of screws	High-alloy stainless steel
Material number of screw	1.4301
Product weight	1500 g
Degree of protection	IP65
Corrosion resistance class (CRC)	1 - Low corrosion stress