


# Flange mounting EAHH-V2-80-R1

Part number: 1502306

FESTO



## Data sheet

Feature	Value
Size	80
Based on norm	ISO 15552
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils Metals with more than 1% copper as an alloy component are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils Metals with more than 5% copper by mass are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils Metals with more than 5% copper as an alloy component are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils Metals with more than 5% copper, zinc or nickel by mass are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Max. load capacity	12 kN
Product weight	1360 g
Note on materials	RoHS-compliant
Plate material	High-alloy stainless steel
Material of screws	High-alloy stainless steel