


Air solenoid valve

VZWF-B-L-M22C-N12-135-3AP4-10-R1

Part number: 1492360



Data sheet

| Feature | Value |
|----------------------------------|---|
| Structural design | Diaphragm valve Force pilot operated |
| Actuation type | Electrical |
| Sealing principle | Soft |
| Mounting position | Magnet, upright |
| Type of mounting | Line installation |
| Fitting connection | 1/2 NPT |
| Electrical connection | Form A Plug as per EN 175301-803 Rectangular design |
| Nominal width | 13.5 mm |
| Valve function | 2/2, closed, monostable |
| Manual override | None |
| Flow direction | Non-reversible |
| Medium | Compressed air as per ISO 8573-1:2010 [7:::] Inert gas Mineral oil Water Neutral liquids Other flow media on request |
| Nominal pressure of fitting PN | 40 |
| Pressure difference | 0 MPa 0 psi |
| Differential pressure | 0 bar |
| Coil characteristics | 230 V AC: 50/60 Hz, initial power 18.0 VA, holding power 15.0 VA |
| Permissible voltage fluctuations | +/- 10 % |
| Medium pressure | 0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi |

| Feature | Value |
|--|---|
| Max. viscosity | 22 mm ² /s |
| Temperature of medium | -10 °C...80 °C |
| Ambient temperature | -10 °C...35 °C |
| Leak rate to EN 12266-1 | A |
| Flow rate Kv | 2.5 m ³ /h |
| Standard nominal flow rate | 2660 l/min |
| On switching time | 130 ms |
| Switching time off | 180 ms |
| Note on materials | RoHS-compliant |
| LABS (PWIS) conformity | VDMA24364 zone III |
| Housing material | Cast stainless steel |
| Material number of housing | 1.4581 |
| Seals material | NBR |
| Material of screws | High-alloy stainless steel |
| Material number of screw | 1.4301 |
| Product weight | 1000 g |
| CE marking (see declaration of conformity) | as per EU pressure equipment directive As per EU low voltage directive |
| UKCA marking (see declaration of conformity) | according to UK regulations for pressure equipment To UK instructions for electrical equipment |
| Degree of protection | IP65 |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |