

Timer PZVT-30-SEC

Part number: 150238

FESTO



Data sheet

| Feature | Value |
|--|--|
| Structural design | Mechanical sequence counter with pneumatic actuator |
| Switch-off pressure | 0.1 bar |
| Operating pressure | 2 bar...6 bar |
| Switch-on pressure | 1.6 bar |
| Standard nominal flow rate | 50 l/min |
| Adjustable delay time | 2 s...30 s |
| Setting accuracy | ± 0.6 s |
| Pause period for reset | 200 ms |
| Repetition accuracy of time setting | ± 0.3 s |
| Explosion prevention and protection | Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX) |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication not possible |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Degree of protection | IP54 With protective cap and panel frame as per IEC 60529 |
| Ambient temperature | -10 °C...60 °C |
| Product weight | 45 g |
| Type of mounting | Front panel mounting |
| Pneumatic connection | Internal thread M5 |
| Note on materials | RoHS-compliant |
| Housing material | ABS |