

Condensate drain WA-2

Part number: 152810

FESTO



Data sheet

Feature	Value
Actuation type	Mechanical
Mounting position	Vertical +/- 5°
Manual override	Non-detenting
Condensate drain	Fully automatic
Structural design	Fully automatic external mechanics
Measured variable	Fill level
Valve function	2/2, open, monostable
Operating pressure	1.5 bar...14 bar
Operating medium	Water
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-20 °C...60 °C
Temperature of medium	0 °C...50 °C
Ambient temperature	0 °C...50 °C
Product weight	92 g
Type of mounting	Line installation
Condensate drain connection	PK-4
Pneumatic connection	M9
Housing material	Wrought aluminum alloy