

Manifold subbase with 90° connections NAVW-1/2-3-ISO

Part number: 152791

FESTO



Data sheet

Feature	Value
Mounting position	Any
Conforms to standard	ISO 5599-1
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Ester oil < 0.1mg/m ³ , according to ISO 8573-1:2010 [-:-:2]
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-20 °C...80 °C
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	1020 g
Sub-base mounting type	With through-hole
Type of mounting	With through-hole
Pilot air port 12/14	G1/8
Auxiliary pilot air port 12	G1/8
Auxiliary pilot air port 14	G1/8
Pilot air port 12	G1/8
Pilot air port 14	G1/8
Pneumatic connection 1	G1/2
Pneumatic connection 2	G1/2
Pneumatic connection 4	G1/2
Material of sub-base	Die-cast aluminum