

# Push-in fitting QS-1/8-8-I

Part number: 153015

FESTO



## Data sheet

| Feature                                         | Value                                                                    |
|-------------------------------------------------|--------------------------------------------------------------------------|
| Size                                            | Standard                                                                 |
| Nominal width                                   | 5.3 mm                                                                   |
| Type of seal on screwed plug                    | Coating                                                                  |
| Mounting position                               | Any                                                                      |
| Design                                          | Straight design                                                          |
| Pack size                                       | 10                                                                       |
| Structural design                               | Push-pull principle                                                      |
| Operating pressure for entire temperature range | -0.095 MPa...0.6 MPa<br>-0.95 bar...6 bar<br>-13.775 psi...87 psi        |
| Temperature-dependent operating pressure        | -0.095 MPa...1.4 MPa<br>-0.95 bar...14 bar<br>-13.775 psi...203 psi      |
| Information on operating pressure               | Water: max. 0.6 MPa at max. 50 °C                                        |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7::-]<br>Water (liquid, ice-free) |
| Information on operating and pilot media        | Operation with oil lubrication possible                                  |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                                                 |
| LABS (PWIS) conformity                          | VDMA24364-B1/B2-L                                                        |
| Ambient temperature                             | -10 °C...80 °C                                                           |
| Product weight                                  | 8.8 g                                                                    |
| Type of mounting                                | Internal hexagon, AF 5                                                   |
| Pneumatic connection 1                          | External thread R1/8                                                     |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 8 mm                               |
| Releasing ring color                            | Blue                                                                     |
| Note on materials                               | RoHS-compliant                                                           |
| Housing material                                | Brass, nickel-plated                                                     |
| Releasing ring material                         | POM                                                                      |
| Material of tubing seal                         | NBR                                                                      |
| Material of tube retaining claw                 | High-alloy stainless steel                                               |