

# Push-in L-connector QSL-10H-8

Part number: 153063

FESTO



## Data sheet

| Feature                                         | Value                                                                     |
|-------------------------------------------------|---------------------------------------------------------------------------|
| Size                                            | Standard                                                                  |
| Nominal width                                   | 4.9 mm                                                                    |
| Mounting position                               | Any                                                                       |
| Design                                          | L-shape                                                                   |
| Pack size                                       | 10                                                                        |
| Structural design                               | Push-pull principle                                                       |
| Operating pressure for entire temperature range | -0.095 MPa...0.6 MPa<br>-0.95 bar...6 bar<br>-13.775 psi...87 psi         |
| Temperature-dependent operating pressure        | -0.095 MPa...1.4 MPa<br>-0.95 bar...14 bar<br>-13.775 psi...203 psi       |
| Information on operating pressure               | Water: max. 0.6 MPa at max. 50 °C                                         |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-]<br>Water (liquid, ice-free) |
| Information on operating and pilot media        | Operation with oil lubrication possible                                   |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                                                  |
| LABS (PWIS) conformity                          | VDMA24364-B1/B2-L                                                         |
| Cleanroom class                                 | Class 4 according to ISO 14644-1                                          |
| Ambient temperature                             | -10 °C...80 °C                                                            |
| Product weight                                  | 8 g                                                                       |
| Pneumatic connection 1                          | Push-in sleeve Ø 10 mm                                                    |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 8 mm                                |
| Releasing ring color                            | Blue                                                                      |
| Note on materials                               | RoHS-compliant                                                            |
| Housing material                                | PBT                                                                       |
| Releasing ring material                         | POM                                                                       |
| Material of tubing seal                         | NBR                                                                       |
| Material of tube retaining claw                 | High-alloy stainless steel                                                |