

# Predetermining counter PZV-E-C

Part number: 15608

**FESTO**



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Structural design                        | Mechanical sequence counter with pneumatic actuator                |
| Reset method                             | Manual key or pneumatic signal                                     |
| Display                                  | 5-digit                                                            |
| Actuator drop-off pressure               | 0.2 ± 0.1 bar                                                      |
| Resetting cutout pressure                | 0.15 ± 0.1 bar                                                     |
| Actuator response pressure               | 0.6 ± 0.2 bar                                                      |
| Operating pressure                       | 2 bar...8 bar                                                      |
| Minimum resetting pressure               | 2 bar                                                              |
| Min. pulse length for actuator           | 10 ms                                                              |
| Min. pulse length for reset              | 180 ms                                                             |
| Minimum pause period for actuator        | 15 ms                                                              |
| Minimum pause period for reset           | 50 ms                                                              |
| Explosion prevention and protection      | Zone 1 (ATEX)<br>Zone 2 (ATEX)<br>Zone 21 (ATEX)<br>Zone 22 (ATEX) |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication not possible                        |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L                                                  |
| Ambient temperature                      | 0 °C...60 °C                                                       |
| Product weight                           | 150 g                                                              |
| Type of mounting                         | Front panel mounting                                               |
| Pneumatic connection                     | M5                                                                 |