


Compact air cylinder ADVUL-100- -P-A-S6

Part number: 156219

FESTO



Data sheet

Feature	Value
Stroke	1 mm...400 mm
Piston diameter	100 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Variants	Heat-resistant seals max. 120°C
Protection against torsion/guide	Guide rod with yoke
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	0 °C...120 °C
Impact energy in the end positions	1 J
Theoretical force at 6 bar, retracting	4418 N
Theoretical force at 6 bar, advancing	4712 N
Type of mounting	Optionally: With through-hole With accessories
Pneumatic connection	G1/4
Flange screws material	Steel, galvanized
Cover material	Wrought aluminum alloy
Material of dynamic seals	FPM
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy