

# Compact air cylinder AEVU-16- -P-A-S6

Part number: 156251

FESTO



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 1 mm...25 mm   |
| Piston diameter                          | 16 mm  |
| Cushioning                               | Elastic cushioning rings/pads at both ends                         |
| Mounting position                        | Any  |
| Mode of operation                        | Pushing<br>Single-acting   |
| Piston rod end                           | Internal thread  |
| Structural design                        | Piston<br>Piston rod   |
| Position sensing                         | For proximity sensor   |
| Variants                                 | Heat-resistant seals max. 120°C                                    |
| Operating pressure                       | 0.13 MPa...1 MPa<br>1.3 bar...10 bar<br>18.85 psi...145 psi        |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | 0 °C...120 °C  |
| Impact energy in the end positions       | 0.1 J  |
| Theoretical force at 6 bar, advancing    | 111 N  |
| Moving mass at 0 mm stroke               | 12 g   |
| Additional moving mass per 10 mm stroke  | 4 g  |
| Basic weight with 0 mm stroke            | 89 g   |
| Additional weight per 10 mm stroke       | 15 g   |
| Type of mounting                         | Optionally:<br>With through-hole<br>With accessories               |
| Pneumatic connection                     | M5   |
| Flange screws material                   | High-alloy stainless steel   |
| Cover material                           | Wrought aluminum alloy   |
| Material of dynamic seals                | FPM  |
| Piston rod material                      | High-alloy stainless steel   |

| Feature                     | Value                  |
|-----------------------------|------------------------|
| Material of cylinder barrel | Wrought aluminum alloy |