

Compact air cylinder AEVUZ-63- -A-P-A-S6

Part number: 156497

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 1 mm...25 mm |
| Piston diameter | 63 mm |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Single-acting Pulling |
| Piston rod end | External thread |
| Structural design | Piston Piston rod |
| Position sensing | For proximity sensor |
| Variants | Heat-resistant seals max. 120°C |
| Operating pressure | 0.08 MPa...1 MPa 0.8 bar...10 bar 11.6 psi...145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | 0 °C...120 °C |
| Impact energy in the end positions | 0.7 J |
| Theoretical force at 6 bar, advancing | 1679 N |
| Moving mass at 0 mm stroke | 134 g |
| Additional moving mass per 10 mm stroke | 16 g |
| Basic weight with 0 mm stroke | 1059 g |
| Additional weight per 10 mm stroke | 107 g |
| Type of mounting | Optionally: With through-hole With accessories |
| Pneumatic connection | G1/8 |
| Flange screws material | Steel, galvanized |
| Cover material | Wrought aluminum alloy |
| Material of dynamic seals | FPM |
| Piston rod material | High-alloy steel |

| Feature | Value |
|-----------------------------|------------------------|
| Material of cylinder barrel | Wrought aluminum alloy |