

Compact air cylinder ADVULQ-32-80-A-P-A

Part number: 156797

FESTO



Data sheet

| Feature | Value |
|--|--|
| Stroke | 80 mm |
| Piston diameter | 32 mm |
| Cushioning | Elastic cushioning rings/pads at both ends |
| Mounting position | Any |
| Mode of operation | Double-acting |
| Piston rod end | External thread |
| Structural design | Piston Piston rod |
| Position sensing | For proximity sensor |
| Variants | Piston rod at one end |
| Protection against torsion/guide | Square piston rod |
| Operating pressure | 0.1 MPa...1 MPa 1 bar...10 bar 14.5 psi...145 psi |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -20 °C...80 °C |
| Impact energy in the end positions | 0.4 J |
| Theoretical force at 6 bar, retracting | 415 N |
| Theoretical force at 6 bar, advancing | 483 N |
| Moving mass at 0 mm stroke | 49 g |
| Additional moving mass per 10 mm stroke | 9 g |
| Basic weight with 0 mm stroke | 300 g |
| Additional weight per 10 mm stroke | 40 g |
| Type of mounting | Optionally: With through-hole With accessories |
| Pneumatic connection | G1/8 |
| Flange screws material | Steel, galvanized |
| Cover material | Wrought aluminum alloy |

| Feature | Value |
|-----------------------------|----------------------------|
| Material of dynamic seals | NBR TPE-U(PU) |
| Piston rod material | High-alloy stainless steel |
| Material of cylinder barrel | Wrought aluminum alloy |