


Connecting cable SIM-M8-4GD-5-PU

Part number: 158961



Data sheet

Feature	Value
Conforms to standard	EN 61076-2-104 EN 61984
Electrical connection	4-pin/4-wire Straight socket/open end M8x1 / -
DC operating voltage range	0 V...30 V
Operating voltage range AC	0 V...30 V
Current rating at 40° C	4 A
Surge resistance	0.8 kV
Cable length	5 m
Cable characteristic	Standard
Connector cable test conditions	Flexural strength: as per Festo standard Test conditions on request Energy chain > 5 million cycles, bending radius 75 mm
Cable diameter	4.5 mm
Cable design	4 x 0.25 mm ²
Nominal conductor cross section	0.25 mm ²
Wire insulation color code	Blue Brown Black White
Degree of protection	IP65 IP68
Ambient temperature	-25 °C...80 °C
Ambient temperature with flexible cable installation	-5 °C...80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant Halogen-free Free of phosphoric acid ester
Contamination level	3
Corrosion resistance class (CRC)	2 - Moderate corrosion stress

Feature	Value
Material of cable sheath	TPE-U(PU)
Color cable sheath	Gray
Housing material	TPE-U(PU)
Housing colour	Black
Material of union nut	Brass, nickel-plated
Seals material	NBR
Material of pin contacts	Brass, gold-plated
Insulating sheath material	PP