

Compact air cylinder AEVU-40-5-A-P-A

Part number: 157001

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	40 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Pushing Single-acting
Piston rod end	External thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.08 MPa...1 MPa 0.8 bar...10 bar 11.6 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	0.52 J
Theoretical force at 6 bar, advancing	704 N
Moving mass at 0 mm stroke	63 g
Additional moving mass per 10 mm stroke	9 g
Basic weight with 0 mm stroke	433 g
Additional weight per 10 mm stroke	59 g
Type of mounting	With through-hole With accessories Optionally:
Pneumatic connection	G1/8
Flange screws material	Steel, galvanized
Cover material	Wrought aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)

Feature	Value
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy