


Linear actuator DGPL-63- -PPV-A-KF-B

Part number: 161796

FESTO



Data sheet

Feature	Value
Stroke	10 mm...3000 mm
Piston diameter	63 mm
Cushioning	Pneumatic cushioning, adjustable at both ends Pneumatic shock absorber, hard characteristic curve
Mounting position	Any
Guide	Recirculating ball bearing guide
Driver principle	Positive locking (slot)
Position sensing	For proximity sensor
Operating pressure	0.15 MPa...0.8 MPa 1.5 bar...8 bar
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-10 °C...60 °C
Cushioning length	30 mm
Theoretical force at 6 bar, retracting	1870 N
Theoretical force at 6 bar, advancing	1870 N
Moving mass	4990 g
Moving mass at 0 mm stroke	4990 g
Additional moving mass per 10 mm stroke	236 g
Basic weight with 0 mm stroke	15370 g
Alternative connections	See product drawing
Pneumatic connection	G3/8
Cover material	Cast aluminum Coated
Seals material	NBR TPE-U(PU)
Housing material	Aluminum Anodized