



Linear actuator DGPL-18- -PPV-A-GF-B

Part number: 161974
Product to be discontinued

FESTO

For proximity sensing, rodless, with positive-locking connection between piston and actuator and adjustable end-position cushioning at both ends.

Type to be discontinued. Available until 2014. See Support Portal for alternative products.



Data sheet

Feature	Value
Stroke	10 ... 1,800 mm
Piston diameter	18 mm
Cushioning	PPV: Pneumatic cushioning adjustable at both ends YSR: Shock absorber, hard characteristic curve
Assembly position	Any
Guide	Plain-bearing guide
Driver principle	positive-locking (slot)
Position detection	For proximity sensor
Working pressure	2 ... 8 bar
Mode of operation	double-acting
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:::]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	2
Ambient temperature	-10 ... 60 °C
Cushioning length	16 mm
Theoretical force at 6 bar, return stroke	153 N
Theoretical force at 6 bar, advance stroke	153 N
Moving mass	300 g
Moving mass with 0 mm stroke	300 g
Basic weight for 0 mm stroke	750 g
Additional mass factor per 10 mm of stroke	22 g
alternative connections	See product drawing
Pneumatic connection	M5
Materials information for cover	Aluminum casting coated
Materials information for seals	NBR TPE-U(PU)
Materials information, housing	Aluminum Anodized