


# Fine filter combination LFMBA-3/8-D-MIDI

Part number: 162661

FESTO



## Data sheet

| Feature                         | Value  |
|---------------------------------|--|
| Size                            | Midi   |
| Series                          | D  |
| Mounting position               | Vertical +/- 5°  |
| Grade of filtration             | 0.01 µm  |
| Filter efficiency               | 99.9999 %  |
| Condensate drain                | Manually rotating  |
| Structural design               | Fiber filter   |
| Max. condensate volume          | 43 ml  |
| Bowl guard                      | Metal bowl guard   |
| Operating pressure              | 1 bar...16 bar   |
| Operating medium                | Compressed air as per ISO 8573-1:2010 [6:8:4]<br>Inert gas |
| LABS (PWIS) conformity          | VDMA24364-B1/B2-L  |
| Air quality class at the output | Compressed air as per ISO 8573-1:2010 [1:7:2]<br>Inert gas |
| Temperature of medium           | 1.5 °C...60 °C   |
| Residual oil content            | 0.01 mg/m³   |
| Ambient temperature             | -10 °C...60 °C   |
| Product weight                  | 1300 g   |
| Type of mounting                | Line installation<br>With accessories                      |
| Pneumatic connection 1          | G3/8   |
| Pneumatic connection 2          | G3/8   |
| Note on materials               | RoHS-compliant   |
| Compressed air filter material  | Borosilicate fiber   |
| Housing material                | Die-cast zinc  |
| Material of bowl                | PC   |