


Filter

LF-3/8-D-5M-MINI-A

Part number: 162620

FESTO



Data sheet

Feature	Value
Size	Mini
Series	D
Mounting position	Vertical +/- 5°
Grade of filtration	5 µm
Condensate drain	Fully automatic
Structural design	Sinter filter with centrifugal separator
Bowl guard	Metal bowl guard
Operating pressure	2 bar...12 bar
Normal nominal flow rate (normalized to DIN 1343)	1100 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:9:-] Inert gas
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Air quality class at the output	Compressed air as per ISO 8573-1:2010 [6:8:4] Inert gas
Temperature of medium	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	250 g
Type of mounting	Line installation With accessories
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Note on materials	RoHS-compliant
Compressed air filter material	PE
Housing material	Die-cast zinc
Material of bowl	PC