

Push-in T-fitting CRQST-M5-4

Part number: 164200

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	2 mm
Type of seal on screwed plug	Sealing ring
Mounting position	Any
Design	T-shape
Pack size	1
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa...1 MPa -0.95 bar...10 bar -13.775 psi...145 psi
Information on operating pressure	Water: max. 0.6 MPa at max. 50 °C
Operating medium	Compressed air as per ISO 8573-1:2010 [7:...] Water (liquid, ice-free)
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
For use in the food industry	See supplementary material information
Ambient temperature	-15 °C...120 °C
Nominal tightening torque	1.33 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	17 g
No. of outlets	2
No. of supply lines	1
Usable connector cables	PFAN
Type of mounting	External hexagon, AF 10
Pneumatic connection 1	External thread M5
Pneumatic connection 2	for pneumatic tubing outside diameter 4 mm
Material of screwed plug	High-alloy stainless steel
Note on materials	RoHS-compliant
Housing material	High-alloy stainless steel
Material of threaded seal	FPM High-alloy stainless steel

Feature	Value
Releasing ring material	High-alloy stainless steel
Material of tubing seal	FPM
Material of tube retaining claw	High-alloy stainless steel
Thrust ring material	High-alloy stainless steel