



# ISO cylinder DNC-63-400-PPV-A

Part number: 163411

**FESTO**



## Data sheet

| Feature                                  | Value  |
|--|--|
| Stroke                                   | 400 mm   |
| Piston diameter                          | 63 mm  |
| Piston rod thread                        | M16x1.5  |
| Cushioning                               | Pneumatic cushioning, adjustable at both ends                      |
| Mounting position                        | Any  |
| Conforms to standard                     | ISO 15552  |
| Piston rod end                           | External thread  |
| Structural design                        | Piston<br>Piston rod<br>Profile barrel                             |
| Position sensing                         | For proximity sensor   |
| Variants                                 | Piston rod at one end  |
| Operating pressure                       | 0.06 MPa...1.2 MPa<br>0.6 bar...12 bar                             |
| Mode of operation                        | Double-acting  |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L  |
| Ambient temperature                      | -20 °C...80 °C   |
| Impact energy in the end positions       | 0.5 J  |
| Cushioning length                        | 22 mm  |
| Theoretical force at 6 bar, retracting   | 1682 N   |
| Theoretical force at 6 bar, advancing    | 1870 N   |
| Moving mass at 0 mm stroke               | 663 g  |
| Additional moving mass per 10 mm stroke  | 25 g   |
| Basic weight with 0 mm stroke            | 1709 g   |
| Additional weight per 10 mm stroke       | 73 g   |
| Type of mounting                         | With internal thread<br>With accessories                           |
| Pneumatic connection                     | G3/8   |
| Note on materials                        | RoHS-compliant   |

| Feature                     | Value                                     |
|-----------------------------|---|
| Cover material              | Die-cast aluminum<br>Coated               |
| Seals material              | TPE-U(PU)                                 |
| Piston rod material         | High-alloy steel                          |
| Material of cylinder barrel | Wrought aluminum alloy<br>Smooth anodized |