

# ISO cylinder

## DSBG-63-500-PPVA-N3

Part number: 1646751

FESTO



## Data sheet

| Feature                                  | Value                                                              |
|------------------------------------------|--------------------------------------------------------------------|
| Stroke                                   | 500 mm                                                             |
| Piston diameter                          | 63 mm                                                              |
| Piston rod thread                        | M16x1.5                                                            |
| Cushioning                               | Pneumatic cushioning, adjustable at both ends                      |
| Mounting position                        | Any                                                                |
| Conforms to standard                     | ISO 15552                                                          |
| Piston rod end                           | External thread                                                    |
| Structural design                        | Piston<br>Piston rod<br>Tie rod<br>Cylinder barrel                 |
| Position sensing                         | For proximity sensor                                               |
| Variants                                 | Piston rod at one end                                              |
| Operating pressure                       | 0.04 MPa...1.2 MPa<br>0.4 bar...12 bar                             |
| Mode of operation                        | Double-acting                                                      |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)         | 2 - Moderate corrosion stress                                      |
| LABS (PWIS) conformity                   | VDMA24364-B1/B2-L                                                  |
| Ambient temperature                      | -20 °C...80 °C                                                     |
| Impact energy in the end positions       | 1.3 J                                                              |
| Cushioning length                        | 22 mm                                                              |
| Theoretical force at 6 bar, retracting   | 1682 N                                                             |
| Theoretical force at 6 bar, advancing    | 1870 N                                                             |
| Moving mass                              | 1680 g                                                             |
| Moving mass at 0 mm stroke               | 430 g                                                              |
| Additional moving mass per 10 mm stroke  | 25 g                                                               |
| Product weight                           | 4490 g                                                             |
| Basic weight with 0 mm stroke            | 1740 g                                                             |
| Additional weight per 10 mm stroke       | 55 g                                                               |

| Feature                     | Value                                                   |
|-----------------------------|---------------------------------------------------------|
| Type of mounting            | With internal thread<br>With accessories<br>Optionally: |
| Pneumatic connection        | G3/8                                                    |
| Note on materials           | RoHS-compliant                                          |
| Cover material              | Die-cast aluminum, coated                               |
| Piston seal material        | TPE-U(PU)                                               |
| Material of piston          | Wrought aluminum alloy                                  |
| Piston rod material         | High-alloy steel                                        |
| Piston rod wiper material   | TPE-U(PU)                                               |
| Buffer seal material        | TPE-U(PU)                                               |
| Cushion piston material     | POM                                                     |
| Material of cylinder barrel | Wrought aluminum alloy, smooth-anodized                 |
| Nut material                | Steel, galvanized                                       |
| Material of bearing         | POM                                                     |
| Collar nut material         | Steel, galvanized                                       |
| Tie rod material            | High-alloy steel                                        |