


Mini slide SLS-10-5-P-A

Part number: 170491

FESTO



Data sheet

Feature	Value
Stroke	5 mm
Piston diameter	10 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Ball bearing cage guide
Structural design	Yoke Piston Piston rod Ball roller guide Slide
Position sensing	For proximity sensor
Operating pressure	0.1 MPa...1 MPa 1 bar...10 bar 14.5 psi...145 psi
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...60 °C
Impact energy in the end positions	0.05 Nm
Max. force F _y	220 N
Max. force F _z	220 N
Max. torque M _x	0.6 Nm
Max. torque M _y	0.6 Nm
Max. torque M _z	0.5 Nm
Theoretical force at 6 bar, retracting	39 N
Theoretical force at 6 bar, advancing	47 N
Moving mass	41 g
Product weight	130 g
Alternative connections	See product drawing
Type of mounting	With through-hole

Feature	Value
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy, anodized
Guide material	Steel
Housing material	High-alloy stainless steel