

Guided actuator DFM-20-25-P-A-GF

Part number: 170841

FESTO



Data sheet

Feature	Value
Distance of centre of gravity of payload to yoke plate xs	50 mm
Stroke	25 mm
Piston diameter	20 mm
Drive unit operating mode	Yoke
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Guide	Sliding guide
Structural design	Guide
Position sensing	For proximity sensor
Operating pressure	0.2 MPa...1 MPa 2 bar...10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Cleanroom class	Class 7 according to ISO 14644-1
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	0.2 Nm
Max. force Fy	354.7 N
Max. force Fy static	354.7 N
Max. force Fz	354.7 N
Max. force Fz static	354.7 N
Max. torque Mx	10.29 Nm
Max. static moment Mx	10.29 Nm
Max. torque My	3.37 Nm
Max. static moment My	3.37 Nm
Max. torque Mz	3.37 Nm
Max. static moment Mz	3.37 Nm
Max. permissible torque load Mx as a function of the stroke	1.47 Nm
Max. payload as a function of the stroke at defined distance xs	28 N

Feature	Value
Theoretical force at 6 bar, retracting	141 N
Theoretical force at 6 bar, advancing	188 N
Moving mass	400 g
Product weight	806 g
Alternative connections	See product drawing
Pneumatic connection	M5
Note on materials	RoHS-compliant
Cover material	Wrought aluminum alloy
Seals material	NBR
Housing material	Wrought aluminum alloy
Piston rod material	High-alloy stainless steel