


Angle gripper HGW-10-A

Part number: 174818

FESTO

Self-centering, can be used as internal and external gripper, 40° opening angle. Magnetic piston for proximity position sensing. Type to be discontinued. Available until 2011.



Data sheet

Feature	Value
Size	10
Max. replacement accuracy	0.2 mm
Max. opening angle	40 deg
Repetition accuracy, gripper	≤ 0.04 mm
Number of gripper fingers	2
Mode of operation	double-acting
Gripper function	Angle
Design structure	Lever
Position detection	For proximity sensor
Working pressure	2 ... 8 bar
Max. operating frequency of gripper	4 Hz
Min. opening time at 6 bar	5 ms
Min. closing time at 6 bar	5 ms
Operating medium	Filtered compressed air
Corrosion resistance classification CRC	2
Ambient temperature	5 ... 60 °C
Total gripping torque at 6 bar, opening	25 Ncm
Total gripping torque at 6 bar, closing	22 Ncm
Max. force on gripper jaw Fz static	16 N
Max. torque at gripper Mx static	0.3 Nm
Max. torque at gripper My static	0.1 Nm
Max. torque at gripper Mz static	0.2 Nm
Product weight	39 g
Mounting type	with internal (female) thread
Pneumatic connection	M3
Materials note	Free of copper and PTFE
Materials information for cover cap	POM
Materials information, housing	Aluminum Nickel plated
Materials information for gripper jaws	Tool steel Nickel plated