

# Compact air cylinder ADVU-125-80-A-P-A

Part number: 175770

**FESTO**



## Data sheet

Feature	Value
Stroke	80 mm
Piston diameter	125 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	External thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Variants	Piston rod at one end
Operating pressure	0.05 MPa...1 MPa 0.5 bar...10 bar 7.25 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	3.3 J
Theoretical force at 6 bar, retracting	6881 N
Theoretical force at 6 bar, advancing	7363 N
Moving mass at 0 mm stroke	1317 g
Additional moving mass per 10 mm stroke	63 g
Basic weight with 0 mm stroke	3426 g
Additional weight per 10 mm stroke	168 g
Type of mounting	With through-hole With accessories Optionally:
Pneumatic connection	G1/4
Flange screws material	Steel, galvanized
Cover material	Wrought aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)

Feature	Value
Piston rod material	High-alloy steel
Material of cylinder barrel	Wrought aluminum alloy