


Clevis flange SNCB-125-R3

Part number: 176950

FESTO



Data sheet

Feature	Value
Size	125
Based on norm	ISO 15552
Variants	High corrosion protection
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Metals with more than 1% by mass of copper are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils Metals with more than 1% copper as an alloy component are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils Metals with more than 5% copper by mass are excluded from use. Circuit boards, Lines, electrical push-in connectors and Coils Metals with more than 5% copper as an alloy component are excluded from use. Exceptions are printed circuit boards, cables, electrical connectors and coils Metals with more than 5% copper, zinc or nickel by mass are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, circuit boards, cables, electrical plug connectors and coils
Ambient temperature	-40 °C...90 °C
Product weight	1776 g
Note on materials	RoHS-compliant
Mounting material	Die-cast aluminum With protective coating
Bolt material	High-alloy stainless steel
Material of bearing	Polymer
Disc material	Steel, galvanized
Material of screws	High-alloy stainless steel
Fuse material	Spring steel, galvanized