

# Compact air cylinder ADVU-50- -A-P-A-R3

Part number: 176857

**FESTO**



## Data sheet

Feature	Value
Stroke	1 mm...300 mm
Piston diameter	50 mm
Cushioning	Elastic cushioning rings/pads at both ends
Mounting position	Any
Mode of operation	Double-acting
Piston rod end	External thread
Structural design	Piston Piston rod
Position sensing	For proximity sensor
Variants	High corrosion protection
Operating pressure	0.08 MPa...1 MPa 0.8 bar...10 bar 11.6 psi...145 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C...80 °C
Impact energy in the end positions	0.64 J
Theoretical force at 6 bar, retracting	1056 N
Theoretical force at 6 bar, advancing	1178 N
Moving mass at 0 mm stroke	112 g
Additional moving mass per 10 mm stroke	16 g
Basic weight with 0 mm stroke	560 g
Additional weight per 10 mm stroke	72 g
Type of mounting	Optionally: With through-hole With accessories
Pneumatic connection	G1/8
Flange screws material	High-alloy stainless steel
Cover material	Wrought aluminum alloy
Material of dynamic seals	NBR TPE-U(PU)

Feature	Value
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	Wrought aluminum alloy